

Eaton 4436 GGV NK

Catalog Number: 4436 GGV NK

Eaton B-Line series wireway, 4" height, 36" length, 4" width, GGV NK wireway, Thru holes, No knockouts, Screw cover, NEMA 4X, Galvanized steel, Plated screws, Gray, 16 gauge

General specifications



| | |
|-----------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton B-Line series wireway | 4436 GGV NK |
| UPC | Product Length/Depth |
| 782051007084 | 36 in |
| Product Height | Product Width |
| 4 in | 4 in |
| Product Weight | Certifications |
| 9.936 lb | CSA Certified |
| | UL Listed |

Photo is representative

Material/finish

Material thickness

16 gauge

Finish color

Gray

Model

Closure type

Plated screws

Mounting method

Thru holes

Special features

Cover is secured with plated screws

Type

GGV NK wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 4436 GGV NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)