

Eaton 4509-BOX

Catalog Number: 4509-BOX

Eaton Arrow Hart straight blade plug , #18-12 AWG, 20A, Commercial, 250V, Back wire, Yellow, Brass, Vinyl, 6-20P, Two-pole, three-wire, grounding, Screw, 0.25-0.66" in diameter, Vinyl, ED Box

General specifications



Product Name	Catalog Number
Eaton Arrow Hart straight blade plug	4509-BOX
UPC	Product Length/Depth
032664340000	2.5 in
Product Height	Product Width
1.5 in	1.5 in
Product Weight	Warranty
0.1 lb	Refer to warranty document.
Compliances	Certifications
RoHS Compliant	UL NOM Federal Specification Classification 6221 02

Product specifications

Device type

Plug

Color

Yellow

Face/body material

Vinyl

Wiring method

Back wire

Material

Vinyl

Allowable wire size

#18-12 AWG

Amperage Rating

20A

Number Of Poles

Two-pole

Contact material

Brass

Type

Plug

Device grade

Commercial specification grade

NEMA configuration

6-20P

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Resources

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Multimedia

[Commercial and residential straight blade vinyl receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 4509-BOX](#)

Cord range

0.25-0.66" in diameter

Voltage rating

250V

Application

Commercial

Torque rating

15 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)