



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1510 Interstate 30
75087-0000, TX Rockwall
Phone: 469-913-1945
Fax: 469-913-1946



46400 Thermo-Shrink Uf Splice Kit, 14-8 Awg

Ideal

Catalog Number	46400
Manufacturer	Ideal
Description	Uf Splice Kit, 600 V Ac, 8 In Overall Length, 1.1 In Outside Diameter, 0 °C Operating Temperature, +105 °C Operating Temperature, 0.2 LB
Weight per unit	0.2000 (lbs/each)
Product Category	Wire

Features

Cable Size	14 - 8
------------	--------

Descriptions

Description	THERMO-SHRINK UF SPLICE KIT, 14-8 AWG
extra long description	IDEAL 46-400 UF SPLICE KIT
Features	Direct burial rated 14/3 with and without ground thru 8/3 without ground, UF?cable range Stretcher kit repairs a 7 in. to 10 in. section damaged or destroyed by a trencher 600V Maximum, 105°C rating Meets the requirements of the 2002 NEC?Code 110-14(b) and UL486 DUV resistant
Special Features	Features: Direct Burial Rated; Heavy-Wall Heat Shrinkable Tubing - TS-46 Irradiated Cross-Linked Polyolefin With 3:1 Standard Shrink Ratio; Adhesive Liner Provides Complete Insulation And Protection; Simple One-Piece Design Saves Time And Money

Manufacturer Information

Brand	Ideal
GTIN	00783250464005
UPC	783250464005

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	UF Splice Kits

Packaging

Carton	1
Weight Per each	0.2

Uses, Certifications, and Standards

standard	RoHS
----------	------