



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



46401 Thermo-Shrink Underground Splice Kit, 8-4 Awg

Ideal

Catalog Number	46401
Manufacturer	Ideal
Description	Ideal, Underground Splice Kit, Thermo-Shrink, Al/Cu Splice Kits, Cable Size: 8 - 4 Awg, Voltage Rating: 600 V, Operating Temperature: 105 Deg C
Weight per unit	0.1000 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	8 - 4
Voltage Rating	600

Descriptions

Description	THERMO-SHRINK UNDERGROUND SPLICE KIT, 8-4 AWG
extra long description	IDEAL 46-401 UNDERGROUND SPLICE KIT
Features	Direct burial rated, underground splice kitsHeavy-wall heat shrink tubing with adhesive liner provides complete insulation and protectionConnector can be used for aluminum and/or copper cableMeets the requirements of the 2005 NEC?Code 110-14(B)600V maximum, 105°C ratingUV resistant
Long Description	IDEAL, Underground Splice Kit, Thermo-Shrink, Al/Cu Splice Kits, Cable Size: 8 - 4 AWG, Voltage Rating: 600 V, Operating Temperature: 105 DEG C
Product Type	Underground Splice Kit
Special Features	Features: Direct Burial Rated; Heavy-Wall Heat Shrinkable Tubing - TS-46 Irradiated Cross-Linked Polyolefin With 3:1 Standard Shrink Ratio; Adhesive Liner Provides Complete Insulation And Protection; Simple One-Piece Design Saves Time And Money

Manufacturer Information

Brand	Ideal Industries
GTIN	00783250464012
Manufacturers Part Number	46-401
UPC	783250464012

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	Al/Cu Splice Kits

Packaging

Carton	1
Weight Per each	0.1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Operating Temperature	105
standard	RoHS