ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



46403 Thermo-Shrink Uf Splice Kit, 1/0 to 250 MCM

Ideal

Catalog Number	46403
Manufacturer	Ideal
Description	Ideal, Underground Splice Kit, Thermo-Shrink, Al/Cu Splice Kits, Cable Size: 1/0 Awg - 250 Kcmil, Voltage Rating: 600 V, Operating Temperature: 105 Deg C
Weight per unit	0.8000 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	1/0 AWG - 250 KCMIL
Voltage Rating	600

Descriptions

Description	THERMO-SHRINK UF SPLICE KIT, 1/0 TO 250 MCM
extra long description	IDEAL 46-403 Underground Splice Kit
Features	Direct burial rated, underground splice kitsHeavy-wall heat shrink tubing with adhesive liner provides complete insulation and protectionConnector can be used for aluminum and/or copper cableMeets the requirements of the 2005 NEC?Code 110-14(B)600V maximum, 105°C ratingUV resistant
Long Description	IDEAL, Underground Splice Kit, Thermo-Shrink, Al/Cu Splice Kits, Cable Size: 1/0 AWG - 250 KCMIL, Voltage Rating: 600 V, Operating Temperature: 105 DEG C
Product Type	Underground Splice Kit, Ideal, Thermo-Shrink, 1/0 Awg - 250 KCM
Special Features	Features: Direct Burial Rated; Heavy-Wall Heat Shrinkable Tubing - TS-46 Irradiated Cross-Linked Polyolefin With 3:1 Standard Shrink Ratio; Adhesive Liner Provides Complete Insulation And Protection; Simple One-Piece Design Saves Time And Money

Manufacturer Information

Brand	Ideal Industries
GTIN	00783250464036
Manufacturers Part Number	46-403
UPC	783250464036

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	Al/Cu Splice Kits

Packaging

Carton	1
Weight Per each	0.8

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Operating Temperature	105
standard	RoHS