



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 South Persimmon Street
77375-6855, TX Tomball
Phone: 281-357-5300
Fax: 281-357-5005



46405 Thermo-Shrink Underground Splice Kit, 2-8 Awg

Ideal

Catalog Number	46405
Manufacturer	Ideal
Description	Ideal, Butt Splice Kit, Thermo-Shrink, Copper Butt Splice Kits, Cable Size: 8 - 2 Awg, Voltage Rating: 600 V, Operating Temperature: 105 Deg C
Weight per unit	0.1000 (lbs/each)
Product Category	Insulating Materials

Features

Cable Size	8 - 2
Voltage Rating	600

Descriptions

Description	THERMO-SHRINK UNDERGROUND SPLICE KIT, 2-8 AWG
extra long description	IDEAL 46-405 Butt Splice Kit,Ideal,
Features	UL?ListedUV resistantProvides a fully-insulated butt splice600V Maximum, 105°C rating
Long Description	IDEAL, Butt Splice Kit, Thermo-Shrink, Copper Butt Splice Kits, Cable Size: 8 - 2 AWG, Voltage Rating: 600 V, Operating Temperature: 105 DEG C
Product Type	Butt Splice Kit, Ideal, Thermo-Shrink, Cu Butt, UI Listed, 8 - 2
Special Features	Features: UL Listed; Provides A Fully-Insulated Butt Splice; 600V Maximum, 105 DEGC Rating

Manufacturer Information

Brand	Ideal
GTIN	00783250611416
Manufacturers Part Number	46-405
UPC	783250611416

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Copper Butt Splice Kits

Packaging

Carton	1
Weight Per each	0.1

Uses, Certifications, and Standards

Operating Temperature	105
standard	UL Listed, RoHS