



46516

F32T8 TL741/HV/ALTO (PK X 30)



Average Life Hours: 36000

Bulb: T8

Color Temperature: 4100 K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 2470 LM

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 32.0 W

Base: Medium Bi-Pin (G13)

Coating: Copolymer

CRI: 78

Initial Lumens: 2600 LM

Length: 48.00 IN

Pack By: 30

Special Features: Shatter-Resistant

UPC: 726585465163





46516

F32T8 TL741/HV/ALTO (PK X 30)



Average Life Hours: 36000

Bulb: T8

Color Temperature: 4100 K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 2470 LM

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 32.0 W

Base: Medium Bi-Pin (G13)

Coating: Copolymer

CRI: 78

Initial Lumens: 2600 LM

Length: 48.00 IN

Pack By: 30

Special Features: Shatter-Resistant

UPC: 726585465163

