



46546S

FO32/841/ECO (PK X 30)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Medium Bi-Pin (G13)

Coating: Copolymer

Color Temperature: 4100 K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 2775

Package Weight: 15.65 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 32.0 W

Average Life Hours: 30000

Bulb: T8

Color: 841

CRI: 85

Initial Lumens: 2950

Length: 48.00 IN

Package (LxWxH): 49.80 IN x 6.50 IN x 7.90 IN

Pack By: 30

Special Features: Shatter-Resistant

UPC: 726585001040

ULEPH,ROHS,NSF Splash Zone