



# 46546S

FO32/841/ECO (PK X 30)



**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Base:** Medium Bi-Pin (G13)

**Coating:** Copolymer

**Color Temperature:** 4100K

**Diameter:** 1.00 IN

**Lamp Type:** Fluorescent

**Mean Design Lumens:** 2775

**Package Weight:** 15.65 L

**Shape:** T

**Type:** Straight Linear Fluorescent Lamp

**Wattage:** 32.0 W

**Average Life Hours:** 30000

**Bulb:** T8

**Color:** 841

**CRI:** 85

**Initial Lumens:** 2950

**Length:** 48.00 IN

**Package (LxWxH):** 49.80 IN x 6.50 IN x 7.90 IN

**Pack By:** 30

**Special Features:** Shatter-Resistant

**UPC:** 726585001040

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone