

Eaton 483612-SD

Catalog Number: 483612-SD

Eaton B-Line series wall mounted panel enclosure,48" height,12" length,36" width,NEMA 4,Hinged cover,SD enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	483612-SD
	UPC
	782051092110
Product Length/Depth	Product Height
12 in	48 in
Product Width	Product Weight
36 in	120.7 lb

Certifications

UL 50
CSA C22.2.
NEMA

defaultTaxonomyAttributeLabel

Country of origin

US

Special features

1/4 turn with 3-pt latching

Style

Medium single door

Finish color

Painted

Color

ANSI 61 gray

NEMA Rating

4

Cover type

Hinged

Wall thickness

14 gauge, 14 gauge

Material

Carbon steel

Model

SD enclosure

Mounting method

Wall

Closure type

Hinged

Mounting hole details

Thru holes, optional external mounting feet

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 483612-SD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)