

Eaton 4867-BOX

Catalog Number: 4867-BOX

Eaton Arrow Hart straight blade plug, #18-12 AWG, 15A, 125V, Back wire, Yellow, Brass, Vinyl, 5-15P, Two-pole, Three-wire, Screw, Vinyl,

General specifications



Product Name	Catalog Number
Eaton Arrow Hart straight blade plug	4867-BOX
UPC	Product Length/Depth
032664340901	2.5 in
Product Height	Product Width
1.5 in	1.5 in
Product Weight	Compliances
0.105 lb	RoHS Compliant
Certifications	
UL	
NOM	
Federal Specification Classification 6221	
02	

Product specifications

Special features

Angled body

Device type

Plug

Color

Yellow

Face/body material

Vinyl

Wiring method

Back wire

Features

Angled body

Material

Vinyl

Allowable wire size

#18-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Device grade

Commercial

NEMA configuration

5-15P

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Resources

Brochures

Wiring Devices Buyer's Guide

Catalogs

Arrow Hart Buyers Guide Section B

Multimedia

Commercial and residential straight blade vinyl receptacles

Specifications and datasheets

Eaton Specification Sheet - 4867-BOX

Two-pole, three-wire, grounding

Voltage rating

125 V

Application

Commercial

Torque rating

15 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)