

Eaton 4887-BOX

Catalog Number: 4887-BOX

Eaton Arrow Hart straight blade connector , #18-12 AWG, 15A, Commercial, 125V, Back wire, Yellow, Brass, Vinyl, 5-15R, Two-pole, three-wire, grounding, Screw, 0.25-0.66", Vinyl, ED Box

General specifications



Product Name

Eaton Arrow Hart straight blade connector

Catalog Number

4887-BOX

UPC

032664341205

Product Length/Depth

2.6 in

Product Height

1.5 in

Product Width

1.5 in

Product Weight

0.001 lb

Compliances

RoHS Compliant

Certifications

UL

NOM

Federal Specification Classification 6221 02

Product specifications

Device type

Connector

Color

Yellow

Face/body material

Vinyl

Wiring method

Back wire

Material

Vinyl

Allowable wire size

#18-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Connector

Device grade

Commercial specification grade

NEMA configuration

5-15R

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Cord range

Resources

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Multimedia

[Commercial and residential straight blade vinyl receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 4887-BOX](#)

0.25-0.66" in diameter

Voltage rating

125V

Application

Commercial

Torque rating

15 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)