

# Juno RLD G4 Series Retrofit LED Trim Modules

Reintroducing the Juno RLD Series – Now T20 Compliant!

- New Juno RLD G4 Retrofit Trims are T20 compliant for California
- Save more energy! Improved electrical performance equals better efficacy
- Economical and fully featured with same “below the ceiling” aesthetics (new G4 matches existing RLD Trim Modules)
- Dedicated trim sizes for true aperture aesthetics
- Available in 2700K and 3000K
- Durable die-cast aluminum all-in-one design
- Crisp baffle grooves and deep source regression minimizes glare and ceiling brightness
- Dimmable to 5% with incandescent, magnetic low-voltage, or electronic low-voltage wall box dimmers
- Rated Service Life of 50,000 hours
- 5 Year Limited Warranty



## Juno RLD G4 Series Retrofit LED Trim Modules Crossover

Size	Phase Out UPC	Phase Out Catalog Number	Phase Out CI Code	New UPC	New Catalog Number	New CI Code
4" RLD	00190887658354	4RLD G3 06LM 27K 90CRI 120 FRPC WWH M6	*251P4C	00194994892700	4RLD G4 06LM 27K 90CRI 120 FRPC WWH M6	*269WYF
4" RLD	00193048238549	4RLD G3 06LM 27K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J1F	00194994892700	4RLD G4 06LM 27K 90CRI 120 FRPC WWH M6	*269WYF
4" RLD	00190887658422	4RLD G3 06LM 30K 90CRI 120 FRPC WWH M6	*251P4L	00194994892472	4RLD G4 06LM 30K 90CRI 120 FRPC WWH M6	*269WXX
4" RLD	00193048238617	4RLD G3 06LM 30K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J1K	00194994892472	4RLD G4 06LM 30K 90CRI 120 FRPC WWH M6	*269WXX
4" RLD	00190887658477	4RLD G3 06LM 35K 90CRI 120 FRPC WWH M6	*251P4T	00194994892472	No direct cross - use *269WXX for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XR2	
4" RLD	00193048238631	4RLD G3 06LM 35K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J1M	00194994892472	No direct cross - use *269WXX for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XR2	
4" RLD	00190887658408	4RLD G3 09LM 27K 90CRI 120 FRPC WWH M6	*251P4J	00194994892755	4RLD G4 09LM 27K 90CRI 120 FRPC WWH M6	*269WYN
4" RLD	00193047890007	4RLD G3 09LM 27K 90CRI 120 FRPC WWH L/SKTWHIP M6	*256KWG	00194994892755	4RLD G4 09LM 27K 90CRI 120 FRPC WWH M6	*269WYN
4" RLD	00190887658453	4RLD G3 09LM 30K 90CRI 120 FRPC WWH M6	*251P4P	00194994892854	4RLD G4 09LM 30K 90CRI 120 FRPC WWH M6	*269WYY
4" RLD	00193048238655	4RLD G3 09LM 30K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J1P	00194994892854	4RLD G4 09LM 30K 90CRI 120 FRPC WWH M6	*269WYY
4" RLD	00190887658484	4RLD G3 09LM 35K 90CRI 120 FRPC WWH M6	*251P4U	00194994892854	No direct cross - use *269WYY for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XR2	
4" RLD	00193048238686	4RLD G3 09LM 35K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J1W	00194994892854	No direct cross - use *269WYY for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XR2	
5" RLD	00190887658507	5RLD G3 07LM 27K 90CRI 120 FRPC WWH M6	*251P4W	00194994892892	5RLD G4 07LM 27K 90CRI 120 FRPC WWH M6	*269X05
5" RLD	00193048238815	5RLD G3 07LM 27K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J2F	00194994892892	5RLD G4 07LM 27K 90CRI 120 FRPC WWH M6	*269X05
5" RLD	00190887658545	5RLD G3 07LM 30K 90CRI 120 FRPC WWH M6	*251P51	00194994892939	5RLD G4 07LM 30K 90CRI 120 FRPC WWH M6	*269X07
5" RLD	00193048238884	5RLD G3 07LM 30K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J2K	00194994892939	5RLD G4 07LM 30K 90CRI 120 FRPC WWH M6	*269X07
5" RLD	00190887658613	5RLD G3 07LM 35K 90CRI 120 FRPC WWH M6	*251P58	00194994892939	No direct cross - use *269X07 for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XRC	
5" RLD	00193048238914	5RLD G3 07LM 35K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J2S	00194994892939	No direct cross - use *269X07 for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XRC	
5" RLD	00190887658521	5RLD G3 09LM 27K 90CRI 120 FRPC WWH M6	*251P4Y	00194994892892	No direct cross - use *269X05 for closest RLD replacement	
5" RLD	00193047890144	5RLD G3 09LM 27K 90CRI 120 FRPC WWH L/SKTWHIP M6	*256KX5	00194994892892	No direct cross - use *269X05 for closest RLD replacement	
5" RLD	00190887658583	5RLD G3 09LM 30K 90CRI 120 FRPC WWH M6	*251P55	00194994892939	No direct cross - use *269X07 for closest RLD replacement	
5" RLD	00193048238938	5RLD G3 09LM 30K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J2V	00194994892939	No direct cross - use *269X07 for closest RLD replacement	
5" RLD	00190887658637	5RLD G3 09LM 35K 90CRI 120 FRPC WWH M6	*251P5A	00194994892939	No direct cross - use *269X07 for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XRC	
5" RLD	00193048238976	5RLD G3 09LM 35K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J2X	00194994892939	No direct cross - use *269X07 for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XRC	
6" RLD	00190887658767	6RLD G3 07LM 27K 90CRI 120 FRPC WWH M6	*251P5G	00194994892953	6RLD G4 07LM 27K 90CRI 120 FRPC WWH M6	*269X0A
6" RLD	00193048238990	6RLD G3 07LM 27K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J31	00194994892953	6RLD G4 07LM 27K 90CRI 120 FRPC WWH M6	*269X0A
6" RLD	00190887658828	6RLD G3 07LM 30K 90CRI 120 FRPC WWH M6	*251P5N	00194994892991	6RLD G4 07LM 30K 90CRI 120 FRPC WWH M6	*269X0G
6" RLD	00193048239072	6RLD G3 07LM 30K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J37	00194994892991	6RLD G4 07LM 30K 90CRI 120 FRPC WWH M6	*269X0G
6" RLD	00190887658903	6RLD G3 07LM 35K 90CRI 120 FRPC WWH M6	*251P60	00194994892991	No direct cross - use *269X0G for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XRC	
6" RLD	00193048239089	6RLD G3 07LM 35K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J3E	00194994892991	No direct cross - use *269X0G for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XRC	
6" RLD	00190887658798	6RLD G3 10LM 27K 90CRI 120 FRPC WWH M6	*251P5K	00194994893011	6RLD G4 10LM 27K 90CRI 120 FRPC WWH M6	*269X0J
6" RLD	00193047890236	6RLD G3 10LM 27K 90CRI 120 FRPC WWH L/SKTWHIP M6	*256KXF	00194994893011	6RLD G4 10LM 27K 90CRI 120 FRPC WWH M6	*269X0J
6" RLD	00190887658842	6RLD G3 10LM 30K 90CRI 120 FRPC WWH M6	*251P5R	00194994893035	6RLD G4 10LM 30K 90CRI 120 FRPC WWH M6	*269X0M
6" RLD	00193048239096	6RLD G3 10LM 30K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J3F	00194994893035	6RLD G4 10LM 30K 90CRI 120 FRPC WWH M6	*269X0M
6" RLD	00190887658934	6RLD G3 10LM 35K 90CRI 120 FRPC WWH M6	*251P63	00194994893035	No direct cross - use *269X0M for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XRC	
6" RLD	00193048239102	6RLD G3 10LM 35K 90CRI 120 FRPC WWH L/SKTWHIP M6	*259J3G	00194994893035	No direct cross - use *269X0M for closest RLD replacement or for 35K suggest Juno E Series 5CCT *266XRC	

