



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4509 Texoma Parkway  
75090-0000, TX Sherman  
Phone: 903-892-8041  
Fax: 903-892-8907



## 4SLSTP4040DDUNV 4' 43W Led Strip 40K 4000LM

*Cooper Lighting Solutions*

Catalog Number	4SLSTP4040DDUNV
Manufacturer	Cooper Lighting Solutions
Description	Linear Led Striplight, 120 to 277 V, 0.36 A @120 V;0.15 A @ 277, 44 W, Cold Rolled Steel, White, 4000 K, 80, 50000 H Average Life, Dimmable, Painted, 4760 LM Brightness (Lumens), 46-1/2 In Length, 2-7/16 In Width, 2-7/16 In Height, 4.6 LB
Weight per unit	6.5 (lbs/each)
Product Category	Led Surface Architectural & SP

### Features

amperage rating	0.155
Lamp Type	LED
lumens	4927
Number of Lamps	1
Socket Type	N/A
Wattage	41

### Dimensions and Weight

Size	47.244 IN Length 3.74 IN Width 3.74 IN Height
------	---

### Descriptions

Description	4' 43W LED STRIP 40K 4000LM
extra long description	CLS 4SLSTP4040DD-UNV 4SLSTP4040DD-U

### Manufacturer Information

Brand	METALUX
GTIN	00080083705825
UPC	080083705825

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Strip

### Packaging

Carton	1
Weight Per each	6.5

### Uses, Certifications, and Standards

Mounting	Surface/Pendant/Wall Mount
standard	CSA Certified;UL/cULus Listed