



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



50T4QCL12V Lamp I 50T4Q/CL-12V

Sylvania-Ledvance

Catalog Number	50T4QCL12V
Manufacturer	Sylvania-Ledvance
Description	OBS58675 Tungsten Halogen Quartz Bi Pin Standard Low Pressure Clear Finish Uv Filter With Transverse Filament GY6.35 Bi Pin Base 50WATT 12VOLT 2000HR Lamp Life
Weight per unit	0.0200 (lbs/each)
Product Category	Lighting

Features

average life	2000
Base	GY6.35 Bipin
dimnable	Yes
Lamp Type	SINGLE END
lumens	910
Shape	T12
start type	Instant
Voltage Rating	12
Wattage	50

Material, Color, and Finish

color rendering index (cri)	100
color temperature	3000
Finish	Clear

Descriptions

Description	LAMP I 50T4Q/CL-12V
extra long description	SYL 50T4Q/CL-12V/58675 50T4QCL 12V
Long Description	OBS58675 Tungsten Halogen Quartz Bi Pin STANDARD Low Pressure Clear Finish UV Filter With Transverse Filament GY6.35 Bi Pin Base 50Watt 12Volt 2000Hr Lamp Life
Product Type	50T4QCL 12V 40/CS 1/Sku

Manufacturer Information

Brand	Sylvania (Usc)
GTIN	00046135586750
Manufacturers Part Number	50T4Q/CL-12V/58675
sub brand	STANDARD Bi-Pin
UPC	046135586750

Taxonomies, Classifications, and Categories

Category Description	QUARTZ
Type	HALOGEN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
--------	---

Weight Per each	0.02
-----------------	------

Uses, Certifications, and Standards

Application	Medium Screwbase or bi-pin
-------------	----------------------------