



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 50UNPRINTED2X100 Vinyl Corrosion Protection Tape, 2" X 100', BK *Minnesota Mining (3M)*

|                  |                                    |
|------------------|------------------------------------|
| Catalog Number   | 50UNPRINTED2X100                   |
| Manufacturer     | Minnesota Mining (3M)              |
| Description      | 3M 7000057502 3M™ Scotchrap™ Vinyl |
| Weight per unit  | 0.1312 (lbs/each)                  |
| Product Category | 20220415162526                     |

### Descriptions

|                  |   |
|------------------|---|
| Description      | VINYL CORROSION PROTECTION TAPE, 2" X 100', BK  |
| Features         | 3M™ Scotchrap™ Tape 50 is a premium grade, 10 mil thick, all weather, PVC backing tape. It withstands temperatures of 55 to 176 °F ( 48 to 80 °C). This high tack adhesive tape offers resistance to corrosion, impact, abrasion and puncture, making it suitable for use on metal piping systems, conduits and fittings both above and below ground. |
| Long Description | 3M 7000057502 3M™ Scotchrap™ Vinyl  |
| Product Type     | 3M™ Scotchrap™ Vinyl Corrosion Protection Tape 50   |

### Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | Minnesota Mining (3M) |
| GTIN                      | 00054007111566        |
| Manufacturers Part Number | 50UP-2X100FT          |
| UPC                       | 054007111566          |

### Taxonomies, Classifications, and Categories

|                      |                          |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
|----------------------|--------------------------|

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 10     |
| Weight Per each | 0.1312 |