

# Non-Plenum Electronic Wire

## Unshielded Electronic Wire



51104



51114

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
53101	22/2 stranded BC (7/30)	22	2	CMR CL3R	7 lbs	0.110"	1,000' Box (46)	White (01)
53112	22/4 stranded BC (7/30)	22	4	CMR CL3R	13 lbs	0.127"	1,000' Box (46)	White (01)
51116	22/6 stranded BC (7/30)	22	6	CMR CL3R	19 lbs	0.161"	500' Box (45) 1,000' Box (46)	Gray (09)
51118	22/8 stranded BC (7/30)	22	8	CMR CL3R	24 lbs	0.174"	500' Box (45)	Gray (09)
51120	22/10 stranded BC (7/30)	22	10	CMR CL3R	32 lbs	0.202"	1,000' Reel (06)	Gray (09)
51122	22/12 stranded BC (7/30)	22	12	CMR CL3R	35 lbs	0.209"	500' Box (45)	Gray (09)
51104	18/2 stranded BC (7/0.0152)	18	2	CMR CL3R	15 lbs	0.142"	500' Box (45) 1,000' Box (46)	White (01) Gray (09)
51109	18/3 stranded BC (7/0.0152)	18	3	CMR CL3R	21 lbs	0.151"	1,000' Box (46)	Gray (09)
51114	18/4 stranded BC (7/0.0152)	18	4	CMR CL3R	27 lbs	0.166"	500' Box (45) 1,000' Box (46)	White (01) Gray (09)
51117	18/6 stranded BC (7/0.0152)	18	6	CMR CL3R	41 lbs	0.215"	1,000' Reel (06)	Gray (09)
51119	18/8 stranded BC (7/0.0152)	18	8	CMR CL3R	54 lbs	0.233"	1,000' Reel (06)	Gray (09)
51123	18/12 stranded BC (7/0.0152)	18	12	CMR CL3R	78 lbs	0.275"	500' Reel (05) 1,000' Reel (06)	Gray (09)
51105	16/2 stranded BC (19/0.0117)	16	2	CMR CL3R	23 lbs	0.168"	500' Box (45) 1,000' Box (46)	White (01) Gray (09)
51115	16/4 stranded BC (19/0.0117)	16	4	CMR CL3R	43 lbs	0.203"	500' Box (45) 1,000' Box (46)	Gray (09)
51140	14/2 stranded BC (19/0.0147)	14	2	CMR CL3R	35 lbs	0.206"	1,000' Reel (06)	Gray (09)
51174	14/4 stranded BC (19/0.0147)	14	4	CMR CL3R	65 lbs	0.252"	1,000' Reel (06)	Gray (09)
51142	12/2 stranded BC (19/0.0185)	12	2	CMR CL3R	53 lbs	0.260"	1,000' Reel (06)	Gray (09)