

# Commercial Specification Grade Thermoplastic Wallplates

Standard Size

## Commercial Thermoplastic Wallplates

### FEATURES

- High impact-resistant; non-flammable, unbreakable thermoplastic.
- Flush-fitting, warp-resistant design.
- Screw-Catch™ feature holds plate mounting screw captive for ease of installation.
- Matching mounting screws provided.

### 1 Gang Single Receptacle with 0.406" (10.31mm) Hole




Color	Catalog No.
Almond	5131A
Brown	5131B
Gray	5131GY
Ivory	5131V
Light Almond	5131LA
Red	5131RD
White	5131W

### 1 Gang Duplex Receptacle



Color	Catalog No.
Almond	5132A
Brown	5132B
Gray	5132GY
Ivory	5132V
Light Almond	5132LA
Red	5132RD
White	5132W

### 2 Gang Duplex Receptacle



Color	Catalog No.
Almond	5150A
Brown	5150B
Gray	5150GY
Ivory	5150V
Light Almond	5150LA
Red	5150RD
White	5150W

INDUSTRIAL  
COMMERCIAL  
RESIDENTIAL

## 0-9 WALLPLATES

### TESTING & CODE COMPLIANCE

- UL and cUL Listed, UL File #E33216
- Meets current Federal Specifications as tested to UL 514
- Meets all CSA requirements, C22.2 no. 42.1, CSA file #9294 (4413-02).

### MATERIAL CHARACTERISTICS

Meets flammability requirements per UL 94, V2 rated.  
Temperature Rating: -40°C to 70°C.