




1-Gang Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, Gray

By Bell
Catalog # 5189-0

1-Gang Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, Gray,



Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- Three hole covers supplied with two closure plugs
- 2 closure plugs included
- NEMA 3R rated

General

Color	Gray
Construction	Metallic
Cover Type	Lampholder/Cluster
EU RoHs Exemption	6b
Material	Die Cast Aluminum
Number Of Outlets	3
Number of Gang(s)	1-Gang
Type	Cover
UPC	050169518908

Dimensions

Actual Depth	1.063 in
Height	4.594 in
Weight	0.25 lb
Width	2.844 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514A
Nema Rating	NEMA 3R

Logistics

Carton Quantity	20
Packaging Type	Shrink
Pallet Quantity	3600
Standard Package	20

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - 5186 series, 5189 series](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BELL-5189-0-SPEC-EN | REV 1/2024