



1-Gang Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, Bronze

By Bell
Catalog # 5189-2



1-Gang Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, Bronze

Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Three hole covers supplied with two closure plugs
- Installation hardware, gasket, multilingual instructions, and 2 closure plugs are included
- Three 1/2 in. outlets
- Horizontal or vertical mount

General

Color	Bronze
Construction	Metallic
Cover Type	Lampholder/Cluster
Material	Die Cast Aluminum
Number Of Outlets	3
Number of Gang(s)	1-Gang
Type	Cover
UPC	050169518922

Dimensions

Actual Depth	1.063 in
Height	4.594 in
Weight	0.25 lb
Width	2.844 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514A
Nema Rating	NEMA 3R

Logistics

Carton Quantity	20
Packaging Type	Shrink
Pallet Quantity	3000
Standard Package	20

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - 5186 series, 5189 series](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BELL-5189-2-SPEC-EN | REV 1/2024