



## Round Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, Gray

By Bell  
Catalog # 5197-0



Round Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, Gray

### Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- Three hole covers supplied with two closure plugs
- NEMA 3R rated

### General

Color	Gray
Construction	Metallic
Cover Type	Lampholder/Cluster
EU RoHs Exemption	6b
Material	Die Cast Aluminum
Number Of Outlets	3
Type	Cover
UPC	050169519707

### Dimensions

Actual Depth	1.094 in
Height	4.125 in
Weight	0.34 lb
Width	4.125 in

### Certifications and Compliance

Certified Listed	• UL Listed • CSA Certified
Industry Standard(s)	UL 514A
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	20
Packaging Type	Shrink
Pallet Quantity	3600
Standard Package	20

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Sales Drawings - 5193 series, 5197 series](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BELL-5197-0-SPEC-EN | REV 1/2024