





ROUND & RECTANGULAR CLUSTER COVERS

4 in. Round Cluster Cover - Three Threaded Outlets
N/A

D22



Catalog #: 5197-2

APPLICATIONS

For use with BELL® single gang or round weatherproof boxes
Cluster covers provide an easy means of mounting BELL® lampholders and other accessories.

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- Three hole covers supplied with two closure plugs
- N/A

UL LISTED

Standard 514A

CSA

C22.2 No. 18

NEMA

3R Rated

GENERAL PRODUCT INFORMATION

Color: Bronze

CONFIGURATION

Number Of Outlets: 3

PRODUCT MEASUREMENTS

Outlet Size: 1/2 in.
Wt. Ea. (Lbs.): 0.406

PACKAGING

Package Type:	Shrink
Std. Pkg.:	20
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	40.60
Ship Carton Length (in.):	15.75
Ship Carton Width (in.):	3.88
Ship Carton Height (in.):	8.50
Ctn Weight (Lbs.):	8.12
Pallet Qty:	3000.00
UPC Number:	050169519721
I2of5:	50050169519726