

# Eaton 5223-7V-BU

Catalog Number: 5223-7V-BU

Eaton toggle switch, 15A, Wall, 120V, Side wire, Screw, Ivory, Three-Way



## General specifications

Product Name	Catalog Number
Eaton toggle switch	5223-7V-BU
UPC	Product Length/Depth
032664752179	1.31 in
Product Height	Product Width
3.28 in	0.88 in
Product Weight	Certifications
0.1 lb	UL
	Federal Specification Classification 6241 05

## Product specifications

### Special features

Bulk

### Connector type

Screw

### Switch type

Three-way

### Load type

ELV

Fan

Motor Control

CFL

HAL

MLV

FLR

INC

LED

### Color

Ivory

### Wiring method

Side wire

### Material

Polycarbonate

### Mounting method

Wall

### Allowable wire size

#14-10 AWG

### Amperage Rating

15A

### Number Of Poles

Single-pole

### Type

Toggle switch

### Voltage rating

120 V

### Terminal enclosure material

Brass

### Application

## Resources

### Catalogs

[Residential Buyers Guide B-07](#)

### Specifications and datasheets

[Eaton Specification Sheet - 5223-7V-BU](#)

Residential

Torque rating

14 lbf-inch



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)