

Eaton 5223-7W-BU

Catalog Number: 5223-7W-BU

Eaton toggle switch, 15A, Residential, Wall, 120V, Side wire, Screw, White, Three-Way



General specifications

Product Name	Catalog Number
Eaton toggle switch	5223-7W-BU
UPC	Product Length/Depth
032664752209	1.31 in
Product Height	Product Width
3.28 in	0.88 in
Product Weight	Certifications
0.001 lb	UL Federal Specification Classification 6241 05

Product specifications

Special features

Bulk

Connector type

Screw

Switch type

Three-way

Load type

ELV

INC

HAL

FLR

Motor Control

MLV

CFL

LED

Fan

Color

White

Wiring method

Side wire

Material

Polycarbonate

Mounting method

Wall

Allowable wire size

#14-10 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Type

Toggle switch

Voltage rating

120 V

Terminal enclosure material

Brass

Application

Resources

Catalogs

[Residential Buyers Guide B-07](#)

Specifications and datasheets

[Eaton Specification Sheet - 5223-7W-BU](#)

Residential

Torque rating

14 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia