



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188



523WG 20A 120/277VAC S Wire Comm 3W SW WH

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 523WG |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These Switches Offer Excellent Value While Meeting Federal Specification Standards. External Screw-Pressure-Plate Back Wiring Enables Fast Installation and Superior Electrical Connections. Rugged Construction Shrugs Off Hard Use and Abuse. |
| Weight per unit | 0.1500 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------------|--|
| action | Three pole |
| actuator | Toggle |
| amperage rating | 20 |
| connection | Side Wire or external screw-pressure plate |
| Connection Type | Wired |
| Contact Configuration | One piece brass alloy contact arm |
| Contact Rating | Oversized silver alloy contacts |
| Degree of Protection | 1500V Dielectric Withstand Voltage |
| indoor/outdoor | Indoor |
| insulation | False |
| Load Rating | 20 A @ 120/277 VAC |
| Load Type | Halogen, CFL, LED, Incandescent, Fluorescent, Xenon, Universal |
| Material | Thermoplastic |
| media | Yes |
| Mounting Type | Wall Box |
| Number of Gangs | 1 |
| Number of Switches | 1.0 |
| Poles | 3-way |
| Switch Type | Toggle |
| throw type | Double Throw |
| Voltage | 120 VAC, 277 VAC |
| Voltage Rating | 120/277 |
| Wall Plate Included | NO |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188

Descriptions

| | |
|------------------------|---|
| Description | 20A 120/277VAC S WIRE COMM 3W SW WH |
| extra long description | P&S CS20AC3W 20A 120/277VAC S WIRE |
| Features | Single Piece Plated Steel Mounting Strap |
| Long Description | Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse. |
| Product Type | 20A 120/277VAC S Wire Comm 3W SW W |
| Special Features | Back & Side wire, locking support, one piece brass alloy contact arm |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007126556 |
| Manufacturers Part Number | CS20AC3W |
| UPC | 785007126556 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.15 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Commercial |
| Enclosure | Nylon |
| Mounting | WALL |
| nema rating | WD-1 and WD-6 |
| standard | CULUS, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC |