

Eaton 5266AN

Catalog Number: 5266AN

Eaton Arrow Hart ultra grip straight blade angled plug, #18-12 AWG, 15A, Industrial, 125V, Back wire, Black and white, Brass, Nylon, 5-15P, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Nylon, Core pack

General specifications



Product Name	Catalog Number
Eaton Arrow Hart ultra grip straight blade angled plug	5266AN
	UPC
	032664519512
Product Length/Depth	Product Height
7.5 in	1.5 in
Product Width	Product Weight
4.5 in	0.11 lb
Warranty	Certifications
Refer to warranty document.	UL
	NOM
	Federal Specification Classification 6221 02

Product specifications

Device type

Angled plug

Color

Black and white

Face/body material

Nylon

Wiring method

Back wire

Material

Nylon

Allowable wire size

#18-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Angled plug

Device grade

Extra heavy-duty industrial specification grade

NEMA configuration

5-15P

Style type

Angled body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Resources

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 5266AN](#)

Cord range

0.33-0.66" in diameter

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)