

## Standard Grade Receptacles

2-Pole, 3-Wire Grounding  
15A, 125V/AC



5-15R

### FEATURES

- Patented built-in wire stripper for #14 AWG wire to speed installation.
- High impact-resistant thermoplastic face and back body eliminates breakage.
- Double-wipe ground contacts ensure long-term ground retention.
- Easy access split circuit break-off tab.
- Tri-combo screws accept Slotted-, Phillips-, and Robertson-head tools for installation flexibility.
- Terminal screws backed out and ready for wiring.
- Side wire terminals accept up to #10 AWG solid wire.

## Duplex Receptacles

15A 125V/AC; Push Wire

Description	Color Suffix	Catalog No.	
NEMA 5-15R Duplex Receptacle	V, W	□ 298__	•



Listed to UL498, file no. E15058; CSA certified to C22.2, no. 42; NOM certified



298

## CO/ALR Standard Grade Receptacles

2-Pole, 3-Wire Grounding  
15A, 125V/AC



5-15R

### FEATURES

- For direct connection to aluminum or copper wire.
- Double-wipe ground contacts ensure long-term ground retention.
- Easy access split circuit break-off tab.
- Combination Slotted/Phillips head mounting and terminal screws for installation flexibility.
- Terminal screws backed out and ready for wiring.
- Side wire terminals accept up to #10 solid copper wire or solid aluminum wire.

## CO/ALR Duplex Receptacles

15A 125V/AC; Side Wire

Description	Color Suffix	Catalog No.	
NEMA 5-15R Duplex Receptacle	B, V, W	□ 5270__	•



Listed to UL498, file no. E15058; CSA certified to C22.2, no. 42; NOM certified



5270

**Color Ordering Information:** For ordering devices, include Cat. No. followed by the color code: B (Brown), V (Ivory), W (White)

**Dimensional Information:** B-60

**Specification Information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)

**NAFTA Compliant:** See page F-21