
BELL RACO C HUBBELL

D04

SINGLE GANG BOXES - 2 IN. TO 2-5/8 IN. DEEP

2 in. Deep, with Lugs - Four Threaded Outlets - 4-1/2 in. x 2-3/4 in. N/A $\ensuremath{\mathsf{N/A}}$



Catalog #: 5321-1

APPLICATIONS

For use in branch circuit wiring in wet, damp, or dry locations May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

PRODUCT FEATURES

Reinforced connector outlets

State-of-the-art powder coat finish provides maximum weatherability and scratch resistance Eight box mounting options with detachable lugs Two closure plugs included

Hubs accept all threaded fittings and threaded conduit Ground screw installed

Multi-lingual instructions in each package Includes gasket and mounting hardware

N/A

UL LISTED

File E195978

CSA

C22.2 No. 18

NEMA

3R Rated

GENERAL PRODUCT INFORMATION

GENERAL PRODUCT INFORMATION Color:	White
CONFIGURATION Number Of Outlets: Gangs:	4 1
PRODUCT MEASUREMENTS Depth: Outlet Size: Cubic Inches (cm3): Wt. Ea. (Lbs.):	2 in. 1/2 in. 18.3 (299.9) 0.648
PACKAGING Package Type: Std. Pkg.: Product UPC-A Labeled: Ship Carton Length (in.): Ship Carton Width (in.): Ship Carton Height (in.): Ctn Weight (Lbs.): Pallet Qty: UPC Number: I2of5:	Shrink 20 Yes 16.19 6.50 8.50 12.60 1800.00 050169532119 50050169532114