



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



53511 SGL Recp 20A 125V S-Wire Iv

Pass & Seymour/Legrand

Catalog Number	53511
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Wire Ground Connection, Wall Mount, 1.32 In Length, 1.08 In Width, 3.28 In Height, Thermoplastic, Ivory, Corrosion Resistant, 0.1700 LB
Weight per unit	0.1656 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	SGL RECP 20A 125V S-WIRE IV
extra long description	P&S 53511 RECP SGL 20A 125V S-WIRE

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007535112
Manufacturers Part Number	53511
UPC	785007535112

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.1656

Uses, Certifications, and Standards

Mounting	WALL
Operating Temperature standard	-40°-60°C CULUS, UL 498