



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1800 S. May Ave.
73108-0000, OK Oklahoma City
Phone: 405-896-3723
Fax: 405-272-3057



5361I SGL Recp 20A 125V S+B Wire Iv

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 5361I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Heavy-Duty Spec Grade Single Receptacle, Back and Side Wire, 20A 125V |
| Weight per unit | 0.1830 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| Mounting Type | Box |
| Number of Gangs | 1 |
| Number of Wires | 3 |
| Outlet Type | STRAIGHT BLADE |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wall Plate Included | NO |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.68 |
| Width | 1.093 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1800 S. May Ave.
73108-0000, OK Oklahoma City
Phone: 405-896-3723
Fax: 405-272-3057

Descriptions

| | |
|------------------------|---|
| Description | SGL RECP 20A 125V S+B WIRE IV |
| extra long description | P&S 5361I RECP SGL 20A 125V S+B WIR |
| Features | Single Piece Plated Steel Mounting Strap |
| Long Description | Heavy-Duty Spec Grade Single Receptacle, Back and Side Wire, 20A 125V |
| Product Type | Recp SGL 20A 125V S+B Wire Iv |
| Special Features | Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. One-piece brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for pos |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007536119 |
| Manufacturers Part Number | 5361-I |
| UPC | 785007536119 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.183 |

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| Operating Temperature | -40°-60°C |
| standard | CUL, UL498, FEDSPEC, CSA C22.2 No. 42 |