



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



5362ISP TVSS Recp 20A 125V Alarm Iv *Pass & Seymour/LeGrand*

| | |
|------------------|---|
| Catalog Number | 5362ISP |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Surge Protective Extra Heavy-Duty Duplex Receptacle Offers Increased Transient Protection, Reliability and Protection Notification (Audible Alarm With Led Indicator). Specification Grade Surge Suppressor Receptacle With Audible Alarm and Led Indicator, Ideal For Heavy Duty Power Applications. By Pass and Seymour. Back and Side Wire, 20A, 125V. |
| Weight per unit | 0.3712 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| class | IG |
| connection | Back and side wire |
| indoor/outdoor | Indoor |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Outlet Type | Straight Blade, Surge Protected |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wall Plate Included | NO |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|--------|-------|
| Color | Ivory |
| Finish | Matte |

Dimensions and Weight

| | |
|--------|------|
| Height | 3.75 |
| Width | 1.25 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Descriptions

| | |
|------------------------|---|
| Description | TVSS RECP 20A 125V ALARM IV |
| extra long description | P&S 5362ISP TVSS RECP 20A 125V ALAR |
| Features | Audible Alarm, Indicator Lights |
| Long Description | Surge Protective Extra Heavy-Duty Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Specification grade surge suppressor receptacle with audible alarm and LED indicator, ideal for heavy duty power applications. By Pass and Seymour. Back and Side Wire, 20A, 125V. |
| Product Type | TVSS Recp 20A 125V Alarm Iv |
| Special Features | Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place. LED Indication: steady green = protected, flashing red = not protected, OFF = no power to unit. Audible alarm alert of MOV damage. Alarm able to be turned On/Off. Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation. Impact-resistant nylon exterior resists impacts and scrapes. Triple-wipe, copper-alloy contacts for superior, more dep |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007194388 |
| Manufacturers Part Number | 5362-ISP |
| UPC | 785007194388 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential Switches |
| Type | Spec Grade Surge Protective Receptacle, Audible Alarm with LED Indicator |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.3712 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Uses, Certifications, and Standards

| | |
|-----------------------------------|--|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| Operating Temperature standard | -40°-60°C CULUS, cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/EEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse). |
| Temperature Rating | Operating Temperature: -20°C to +55°C (-4°F to 131°F), Storage Temperature: -40°C to +85°C (-40°F to 185°F) |