



Powering Business Worldwide

### 5369NCR

Conn CR 20A 125V 2P3W Str AutoGrip YL

UPC: 040893018904

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 20 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, PVC Base

Color: Red

NEMA Rating: 5-20R

Connection: Screw

### 5369NHG

Conn HG 20A 125V 2P3W Str AutoGrip BW

UPC: 040893018959

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Single, Straight Blade

Special Features: Premium Hospital Grade, Wiring Type Back and Side Wire

Application: Hospital grade deco

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, Glass Filled Nylon Base

Color: Ivory

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 0.88 X 1.32 X3.28 X4.19IN

Environmental Conditions: See Spec Sheet

Dielectric Strength: 2000 V

Insulation: Nylon Face, Glass Filled Nylon Base

Temperature Rating: -20C to 70C (-4F to 158F)