

# Eaton 5369N

Catalog Number: 5369N

Eaton Arrow Hart auto grip straight blade connector, #16-12 AWG, 20A, Industrial, 125V, Back wire, Black and white, Brass, Nylon, 5-20R, Two-pole, three-wire, grounding, Screw, Nylon, Core pack



## General specifications

Product Name	Catalog Number
Eaton Arrow Hart auto grip straight blade connector	5369N
	UPC 040893018256
Product Length/Depth 4.25 in	Product Height 1.75 in
Product Width 2 in	Product Weight 0.209 lb
Warranty Refer to warranty document.	Certifications cULus Listed

## Product specifications

### Device type

Connector

### Color

White

Black

### Face/body material

Nylon

### Wiring method

Back wire

### Material

Nylon

### Allowable wire size

#16-12 AWG

### Amperage Rating

20A

### Number Of Poles

Two-pole

### Contact material

Brass

### Type

Connector

### Device grade

Extra heavy-duty industrial specification grade

### NEMA configuration

5-20R

### Style type

Straight body

### Design type

Straight blade

### Connection type

Screw

### Number of wires

3

### Receptacle type

Two-pole, three-wire, grounding

## Resources

### Brochures

Wiring Devices Buyer's Guide

### Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

### Specifications and datasheets

Eaton Specification Sheet - 5369N

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

Core pack



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)