
D08



4 IN. ROUND BOX & EXTENSION

1-1/2 in. Deep - Five Threaded Outlets - 4 in. Round Splice Box





Catalog #: 5372-0

APPLICATIONS

For use in branch circuit wiring in wet, damp, or dry locations May be used as a weatherproof junction box, and may be used with BELL® round cluster covers and round lampholder combinations

PRODUCT FEATURES

Reinforced connector outlets

State-of-the-art powder coat finish provides maximum weatherability and scratch resistance Cast-in mounting lugs provide fast, secure installation

Four closure plugs included

Hubs accept all threaded fittings and threaded conduit Ground screw installed

Multi-lingual instructions in each package

Includes gasket and mounting hardware

UL LISTED

File E195978

CSA

C22.2 No. 18

NEMA

3R Rated

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Number Of Outlets: 5

PRODUCT MEASUREMENTS

Depth: Outlet Size: 1-1/2 in. 3/4 in. 16.0 (262.2) Cubic Inches (cm3): Wt. Ea. (Lbs.): 0.580

PACKAGING

Package Type: Std. Pkg.: Product UPC-A Labeled: Weight (Lbs. Per/C): Ship Carton Length (in.): Shrink 16 Yes 58.00 16.19 Ship Carton Width (in.): Ship Carton Height (in.): Ctn Weight (Lbs.): 6.50 8.50 10.15 Pallet Qty: UPC Number: 1440.00 050169537206 12of5: 50050169537201

Page 1 / 1