




## TWO GANG EXTENSION &amp; THREE GANG BOX

2-5/8 in. Deep with Lugs - Seven Threaded Outlets - 4-1/2 in. x 6-3/8 in.  
N/A

D07.1



Catalog #: 5390-0

## APPLICATIONS

For use in branch circuit wiring in wet, damp, or dry locations  
May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

## PRODUCT FEATURES

Reinforced connector outlets  
State-of-the-art powder coat finish provides maximum weatherability and scratch resistance  
Eight box mounting options with detachable lugs  
Four closure plugs included  
Hubs accept all threaded fittings and threaded conduit  
Ground screw installed  
Multi-lingual instructions in each package  
Includes gasket and mounting hardware  
N/A

## UL LISTED

File E195978

## CSA

C22.2 No. 18

## NEMA

3R Rated

## GENERAL PRODUCT INFORMATION

Color: Gray

## CONFIGURATION

Number Of Outlets: 7  
Gangs: 3

## PRODUCT MEASUREMENTS

Depth: 2-5/8 in.  
Outlet Size: 3/4 in.  
Cubic Inches (cm<sup>3</sup>): 55.0 (901.3)  
Wt. Ea. (Lbs.): 1.550

## PACKAGING


Package Type: Boxed  
Std. Pkg.: 1  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 155.00  
Ship Carton Length (in.): 9.25  
Ship Carton Width (in.): 5.75  
Ship Carton Height (in.): 5.00  
Ctn Weight (Lbs.): 1.55  
Pallet Qty: 200.00  
UPC Number: 050169539002  
I2of5: 50050169539007



## TWO GANG EXTENSION &amp; THREE GANG BOX

2-5/8 in. Deep with Lugs - Seven Threaded Outlets - 4-1/2 in. x 6-3/8 in.  
N/A

D07.1



Catalog #: 5390-0

## APPLICATIONS

For use in branch circuit wiring in wet, damp, or dry locations  
May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

## PRODUCT FEATURES

Reinforced connector outlets  
State-of-the-art powder coat finish provides maximum weatherability and scratch resistance  
Eight box mounting options with detachable lugs  
Four closure plugs included  
Hubs accept all threaded fittings and threaded conduit  
Ground screw installed  
Multi-lingual instructions in each package  
Includes gasket and mounting hardware  
N/A

## UL LISTED

File E195978

## CSA

C22.2 No. 18

## NEMA

3R Rated

## GENERAL PRODUCT INFORMATION

Color: Gray

## CONFIGURATION

Number Of Outlets: 7  
Gangs: 3

## PRODUCT MEASUREMENTS

Depth: 2-5/8 in.  
Outlet Size: 3/4 in.  
Cubic Inches (cm<sup>3</sup>): 55.0 (901.3)  
Wt. Ea. (Lbs.): 1.550

## PACKAGING

Package Type: Boxed  
Std. Pkg.: 1  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 155.00  
Ship Carton Length (in.): 9.25  
Ship Carton Width (in.): 5.75  
Ship Carton Height (in.): 5.00  
Ctn Weight (Lbs.): 1.55  
Pallet Qty: 200.00  
UPC Number: 050169539002  
I2of5: 50050169539007