



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2351 Walnut Hill Lane Suite 150
75229-0000, TX Dallas
Phone: 214-351-0785
Fax: 972-241-1564



54806 #4L Cop Conn

Abb Installation Products, Inc

Catalog Number	54806
Manufacturer	Abb Installation Products, Inc
Description	Copper Two-Way Splice, Long Barrel, Max 35KV, Wire Size #4 Awg, Length 1.75 Inches, Diameter 0.39 Inches, Tin Plated, Die Code 29, Die Color Code Gray
Weight per unit	0.0300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V

Material, Color, and Finish

Color	Gray
Finish	Tin-Plated

Descriptions

Description	#4L COP CONN
extra long description	ABB 54806 2WAY CU SPLICE CONN LNGBR
Long Description	Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size #4 AWG, Length 1.75 Inches, Diameter 0.39 Inches, Tin Plated, Die Code 29, Die Color Code Gray
Product Type	2WAY Cu Splice Conn LNGBRL NO4 BRN
Special Features	Two-Way Connectors Provide High Pullout Values, are Easy to Insulate and Provide a Low-Resistance Connection of High Quality and Low Installed Cost

Manufacturer Information

Brand	COLOR-KEYED
GTIN	00786210548067
Manufacturers Part Number	54806
UPC	786210548067

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Splice Connector

Packaging

Carton	50
Weight Per each	0.03

Uses, Certifications, and Standards

Application	Applications certified to 600 V and recommended up to 35 kV
standard	UL E9809 / UL E9809