



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave  
72032-0000, AR Conway  
Phone: 501-336-8444  
Fax: 501-329-5636



## 54807 2AWG 2WAY Cop Conn

*Abb Installation Products, Inc*

Catalog Number	54807
Manufacturer	Abb Installation Products, Inc
Description	Copper Two-Way Splice, Long Barrel, Max 35KV, Wire Size #2 Awg, Length 1.88 Inches, Diameter 0.43 Inches, Tin Plated, Die Code 33, Die Color Code Brown
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
Voltage Rating	600 V

### Material, Color, and Finish

Color	Brown
Finish	Tin-Plated

### Descriptions

Description	2AWG 2WAY COP CONN
extra long description	ABB 54807 2WAY CU SPLICE CONN LNGBR
Long Description	Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size #2 AWG, Length 1.88 Inches, Diameter 0.43 Inches, Tin Plated, Die Code 33, Die Color Code Brown
Product Type	2WAY Cu Splice Conn LNGBRL NO2 BRN
Special Features	Two-Way Connectors Provide High Pullout Values, are Easy to Insulate and Provide a Low-Resistance Connection of High Quality and Low Installed Cost

### Manufacturer Information

Brand	COLOR-KEYED
GTIN	00786210548074
Manufacturers Part Number	54807
UPC	786210548074

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Splice Connector

### Packaging

Carton	25
Weight Per each	0.04

### Uses, Certifications, and Standards

Application	Applications certified to 600 V and recommended up to 35 kV
standard	UL E9809 / UL E9809