



## Irrigation Products

### Standard UF-B Flat Parallel SOL Underground Feeder with Ground



| Part Number | Des          | Str       | Wt/1000' |
|-------------|--------------|-----------|----------|
| 55560-XX-09 | 14/2 w/14 Gr | Solid     | 83       |
| 55561-XX-09 | 14/3 w/14 Gr | Solid     | 186      |
| 55562-XX-09 | 12/2 w/12 Gr | Solid     | 132      |
| 55563-XX-09 | 12/3 w/12 Gr | Solid     | 169      |
| 55564-XX-09 | 10/2 w/10 Gr | Solid     | 176      |
| 55566-XX-09 | 10/3 w/10 Gr | Solid     | 225      |
| 55565-XX-09 | 8/2 w/10 Gr  | 19/.0295" | 250      |
| 55567-XX-09 | 8/3 w/10 Gr  | 7         | 300      |
| 55575-XX-09 | 6/2 w/10 Gr  | 19/.0372" | 340      |
| 55576-XX-09 | 6/3 w/10 Gr  | 7         | 593      |

XX: Insert Appropriate Put-Up Code

PVC Insulation, Put-Up = 1000' (06), 500' (05), Color Code: Gray (09)

### Single-Conductor UF Underground Feeder



| Part Number  | Des    | Wt/1000' | Std Pkg  |
|--------------|--------|----------|----------|
| 54499-XX-YY* | 18 Sol | 14       | 4 x 500  |
| 54500-XX-YY* | 16 Sol | 18       | 4 x 500  |
| 54501-XX-YY  | 14 Sol | 28       | 4 x 500  |
| 54502-XX-YY  | 12 Sol | 38       | 1 x 2500 |
| 54503-XX-YY  | 10 Sol | 53       | 1 x 2500 |
| 54514-XX-YY  | 8 Sol  | 86       | 1 x 2500 |
| 54505-XX-YY  | 6 Str  | 126      | 1 x 2500 |
| 54506-XX-YY  | 4 Str  | 191      | 1 x 2500 |
| 54507-XX-YY  | 2 Str  | 279      | 1 x 2500 |

XX: Insert Appropriate Put-Up Code, YY: Insert Appropriate Color Code, \* No UL Classification

UL Listed Underground Feeder Cable 600 Volt, Type UF, TWU, FT1, Baro-Pak = 2500' (59), 500' (55), Reels = 2500' (09), 500' (05), Color Code = Various

### Water Resistant Fountain Cable



| Part Number | Des  | Wt/1000' | Std Pkg |
|-------------|------|----------|---------|
| 23225-04-08 | 18/2 | 44       | 4 x 250 |
| 23325-04-08 | 18/3 | 55       | 4 x 250 |
| 23425-04-08 | 18/4 | 66       | 4 x 250 |
| 23226-04-08 | 16/2 | 54       | 4 x 250 |
| 23326-04-08 | 16/3 | 67       | 1 x 250 |
| 23426-04-08 | 16/4 | 78       | 1 x 250 |
| 23227-04-08 | 14/2 | 68       | 1 x 250 |
| 23327-04-08 | 14/3 | 84       | 1 x 250 |
| 23427-04-08 | 14/4 | 104      | 1 x 250 |
| 23228-04-08 | 12/2 | 97       | 1 x 250 |
| 23328-04-08 | 12/3 | 123      | 1 x 250 |
| 23428-04-08 | 12/4 | 157      | 1 x 250 |
| 23229-04-08 | 10/2 | 166      | 1 x 250 |
| 23329-04-08 | 10/3 | 216      | 1 x 250 |
| 23429-04-08 | 10/4 | 276      | 1 x 250 |

UL/CSA Listed Type SJEOOW/SJTOOW (TPE), Nec Article 400, 300 Volt, Put-Up = 250' (04), Color Code: Black (08)



### Striped UF-Underground Feeder

| Part Number | Des          | Wt/1000' | Std Pkg      |
|-------------|--------------|----------|--------------|
| 54501-09-YY | 14 Sol       | 28       | 1 x 2500     |
| 54502-09-YY | 12 Sol       | 38       | 1 x 2500     |
| Code        | Color/Stripe | Code     | Color/Stripe |
| 12          | White/Yellow | 61       | Blue/White   |
| 14          | White/Red    | 62       | Blue/Yellow  |
| 16          | White/Blue   | 64       | Blue/Red     |
| 18          | White/Black  | 68       | Blue/Black   |
| 41          | Red/White    | 81       | Black/White  |
| 42          | Red/Yellow   | 82       | Black/Yellow |
| 46          | Red/Blue     | 84       | Black/Red    |
| 48          | Red/Black    | 86       | Black/Blue   |

YY: Insert Appropriate Color Code

UL Listed Underground Feeder Cable 600 Volt Reels = 2500' (09), Color Code = Various

### Low-Voltage Underground Lighting Cable – Baro-Pak™ or Reels



| Part Number  | Des  | Str     | Wt/1000' | Std Pkg |
|--------------|------|---------|----------|---------|
| 55264-XX-08* | 18/2 | 16/30   | 29       | 1 Reel  |
| 55266-XX-08* | 16/2 | 26/30   | 41       | 1 Reel  |
| 55267-XX-08* | 14/2 | 41/30   | 54       | 1 Reel  |
| 55269-XX-08  | 12/2 | 65/30   | 77       | 1 Reel  |
| 55272-XX-08  | 10/2 | 104/30  | 105      | 1 Reel  |
| 55271-XX-08  | 8/2  | 7x24/30 | 161      | 1 Reel  |

XX: Insert Appropriate Put-Up Code, \*No cUL Classification

Stranded Low Energy Lighting Cable, Baro-Pak = 500' (55), 250' (54), Reels = 2500' (09), 1000' (06), 500' (05), 250' (04), Color Code: Black (08)

