



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



553020507 18/2 Thermostat/Bell Wire

Coleman Cable

Catalog Number	553020507
Manufacturer	Coleman Cable
Description	Thermostat Wire, Solid, 2 Conductors, #18 Awg Conductor Size, 150 V, 500 FT Overall Length, 0.132 In Outside Diameter, 0.006 In Insulation Thickness, Copper Conductor Material, Polypropylene Insulation Material, Red;White, -20 °C Operating Temperature, +60 °C Operating Temperature, 14 LB/MFT
Weight per unit	0.0200 (lbs/ft)
Product Category	Jacketed Thermostat Wire & CBL

Features

Stranding	SOLID
-----------	-------

Material, Color, and Finish

Color Code	Red, White
Jacket Color	BROWN
Jacket Material	PVC

Dimensions and Weight

Length	500 FT
Length in ft	500 W
Outer Diameter	0.132 INCH

Descriptions

Commodity Description	Misc Small Wires-Jacketed Thermostat Wire & Cable
Description	18/2 THERMOSTAT/BELL WIRE

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892353803
Model	55302
UPC	029892353803

Taxonomies, Classifications, and Categories

Category Description	BELL WIRE
Type	CM/FT1

Packaging

Carton	500
Package	2000
Weight Per foot	0.02

Uses, Certifications, and Standards

Approval	UL, CUL
Temperature Rating	-20 TO 60 DEG C



PRODUCT DATA SHEET

Controlled Document - Engineering Drive


1530 Shields Drive
Waukegan, IL 60085
Toll-Free (800) 323-9355
Fax: (847) 689-1192

PART NUMBER: 55302
DESCRIPTION: 18/2 SOLID CL2 THERMOSTAT CABLE
CONSTRUCTION: This cable consists of two bare copper insulated conductors with an overall jacket.
APPROVALS: UL Standard 13, NEC Article 725.
APPLICATION: Class 2 Power Limited Circuit Cable Used In Thermostat Control Applications

Construction Parameters:

Cable Cross-Section

Conductor 18 AWG Bare Copper
Stranding Solid
Insulation Material Polypropylene
Insulation Thickness 0.006" Nom.
Insulated Conductor Diameter 0.052" Nom.
Number of Conductors 2
Lay Length Parallel
Jacket Material PVC
Jacket Thickness 0.014" Nom.
Overall Cable Diameter 0.132" Nom.
Approximate Cable Weight 16.3 Lbs/1M' Nom.
Flame Rating UL 1581 Vertical Tray Flame Test



Electrical & Environmental Properties:

Temperature Rating -20°C to 60°C
Operating Voltage 150V Voltage Rating Per National Electric Code Article 725
Capacitance Between Conductors @ 1 KHz 25 pF/ft Nom.
Capacitance Between Conductors to Shield @ 1 KHz -----
DC Resistance per Conductor @ 20°C 6.32 Ohms/1M' Nom.

Insulation Colors Red White
Jacket Color Brown (Other colors available for minimum order)

Legend (Surface Ink Print) TYPE CL2 C(ETL)US (ETL CODE) 18 AWG 2/C BAROSTAT II SUN RES -- CMX
OUTDOOR -- TYPE CMH FT1 XX/XX/XX (MONTH/DAY/YEAR) XXXXXX (W/O #)

This product complies with European Directive 2002/95/EC (RoHS)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

Cable has a rip cord for easy jacket removal

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name _____

Customer Approval _____

Specification Issue Date: March 25, 2009

Packaging Options

Coleman Cable offers four types of packaging options.

- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels


All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

* Not all options are available for each product



Coleman Cable Part Legend

XXXXXX-XX-XX



Put-ups

Put-ups	Code
Reel, 250 ft	04
Reel, 500 ft	05
Reel, 1,000 ft	06
Reel-in-box, 1,000 ft	16
RabbitPull™ Pull-Box, 500 ft	45
RabbitPull™ Pull-Box, 1,000 ft	46
SignaCoil™ 500 ft	55
SignaCoil™ 1,000 ft	56

Colors

Colors	Code	Colors	Code
White	01	Pink	11
Yellow	02	Purple	13
Orange	03	Clear	18
Red	04	Fluorescent	21
Green	05	Pink	21
Blue	06	Ivory	22
Brown	07	Natural	23
Black	08	Beige	33
Gray	09	Red Striped	44
		CorraClad™	44

