

# Modular connectivity points

# Modular jacks & adapters

## **Product description**

Voice, data, Category 3 RJ11, Category 6 RJ45, Category 5E RJ45, RG6 F-Type coax

### **Design features**

- 110 style modular jacks
- Data jacks have 8 positions and 8 conductors for high-speed LAN applications
- Category 3 jacks have 6 positions and 6 conductors for voice and/or data applications
- Category 6 jacks are rated for 650MHz, Category 5E jacks are rated for 160MHz
- IDC termination for simple and fast installation
- Color coding wiring labels for both T568A/B and USOC helps easy selection of products
- Video connectors require no soldering
- All jacks and adapters clip smoothly into place in our flush-mount modular wallplates providing ease of installation



5547-5E



5547-3E



5552-5E



5550-5E

Modular jacks & adapters

Wodulai jacks & adapters				
Description	Features	Color suffix	Catalog no.	(NoHS)
Data jack, category 6 RJ45	8-position, 8-conductor 568A/B wiring	LA, V, W	□ 5546-6	•
Data jack, category 5e RJ45	8-position, 8-conductor 568A/B wiring	BL, LA, V, W	□ 5547-5E	•
Voice jack, category 3 RJ11	6-position, 6-conductor USDOC wiring	LA, V, W	□ 5547-3E	•
Video connector, F-type coax	For RG6 applications TV/satellite	LA, V, W	□ 5552-5E	•
Blank insert	For filling empty portssolid blank face	LA, V, W	□ 5550-5E	•

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: BL (Blue), LA (Light Almond), V (Ivory), W (White)



Specification information: Please visit www.eaton.com/wiringdevices Compliances, specifications and availability are subject to change without notice.