

Eaton 5552-5EV

Catalog Number: 5552-5EV

Eaton Modular jacks and adapters, Coax type F insert adapter, Commercial, residential video applications, Flush, snap-in, Ivory, Modular adapter, Coaxial type F jack, IDC termination, Thermoplastic, 0° to 40°C, RG-6, type F

General specifications



Product Name	Eaton Modular jacks and adapters	Catalog Number	5552-5EV
UPC	032664629488	Product Length/Depth	0.7 in
Product Height	0.8 in	Product Width	1.1 in
Product Weight	0.027 lb	Warranty	Refer to warranty document.
Compliances	RoHS Compliant	Certifications	cULus Listed

Product specifications

Connector type

IDC termination

Device type

Coaxial type F jack

Color

Ivory

Wiring method

RG6

Material

Thermoplastic

Mounting method

Snap-in

Flush

Cable type

RG-6, coaxial type F

Wire type

RG-6, type F

Type

Coax type F insert adapter

Used with

For RG6 applications TV/satellite

Design type

Modular adapter

Operating temperature

0 to 40 °C

Application

Commercial, residential video applications

Resources

Catalogs

[Residential Buyers Guide D-04](#)

Specifications and datasheets

[Eaton Specification Sheet - 5552-5EV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)