

Specifications

Eaton 5666N

Eaton Arrow Hart auto grip straight blade plug, #18-12 AWG, 15A, Industrial, 250V, Back wire, Black and white, Brass, Nylon, 6-15P, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Nylon, Core pack

General specifications

PRODUCT NAME	Eaton Arrow Hart auto grip straight blade plug
CATALOG NUMBER	5666N
UPC	040893021553
PRODUCT LENGTH/DEPTH	1.91 in
PRODUCT HEIGHT	4.13 in
PRODUCT WIDTH	1.78 in
PRODUCT WEIGHT	0.181 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL NOM Federal Specification Classification 6221 02
PRODUCT TYPE	Auto grip



Powering Business Worldwide

Product specifications

DEVICE TYPE	Plug
TYPE	Plug
AMPERAGE RATING	15A
VOLTAGE RATING	250V
CONTACT MATERIAL	Brass
APPLICATION	Industrial
DEVICE GRADE	Extra heavy-duty industrial specification grade
WIRING METHOD	Back wire
NUMBER OF WIRES	3
NUMBER OF POLES	Two-pole
STYLE TYPE	Straight body
CORD RANGE	0.33-0.66" in diameter
MATERIAL	Nylon
PACKAGING TYPE	Core pack
COLOR	Black White
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	#18-12 AWG
NEMA CONFIGURATION	6-15P
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Nylon
RECEPTACLE TYPE	Two-pole, three-wire, grounding

Resources

MULTIMEDIA	Arrow Hart - Connecting Safety to Reliability since 1890
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 5666N Arrow Hart industrial grade straight blade and locking devices brochure

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton 5666N

Eaton Arrow Hart auto grip straight blade plug, #18-12 AWG, 15A, Industrial, 250V, Back wire, Black and white, Brass, Nylon, 6-15P, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Nylon, Core pack

General specifications

PRODUCT NAME	Eaton Arrow Hart auto grip straight blade plug
CATALOG NUMBER	5666N
UPC	040893021553
PRODUCT LENGTH/DEPTH	1.91 in
PRODUCT HEIGHT	4.13 in
PRODUCT WIDTH	1.78 in
PRODUCT WEIGHT	0.181 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL NOM Federal Specification Classification 6221 02
PRODUCT TYPE	Auto grip



Powering Business Worldwide

Product specifications

DEVICE TYPE	Plug
TYPE	Plug
AMPERAGE RATING	15A
VOLTAGE RATING	250V
CONTACT MATERIAL	Brass
APPLICATION	Industrial
DEVICE GRADE	Extra heavy-duty industrial specification grade
WIRING METHOD	Back wire
NUMBER OF WIRES	3
NUMBER OF POLES	Two-pole
STYLE TYPE	Straight body
CORD RANGE	0.33-0.66" in diameter
MATERIAL	Nylon
PACKAGING TYPE	Core pack
COLOR	Black White
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	#18-12 AWG
NEMA CONFIGURATION	6-15P
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	Nylon
RECEPTACLE TYPE	Two-pole, three-wire, grounding

Resources

MULTIMEDIA	Arrow Hart - Connecting Safety to Reliability since 1890
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 5666N Arrow Hart industrial grade straight blade and locking devices brochure

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

