

Specifications

Eaton 5666N

Eaton Arrow Hart auto grip straight blade plug, #18-12 AWG, 15A, Industrial, 250V, Back wire, Black and white, Brass, Nylon, 6-15P, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Nylon, Core pack

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Arrow Hart auto grip straight blade plug |
| CATALOG NUMBER | 5666N |
| UPC | 040893021553 |
| PRODUCT LENGTH/DEPTH | 1.91 in |
| PRODUCT HEIGHT | 4.13 in |
| PRODUCT WIDTH | 1.78 in |
| PRODUCT WEIGHT | 0.181 lb |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | UL NOM Federal Specification Classification 6221 02 |
| PRODUCT TYPE | Auto grip |



Powering Business Worldwide

Product specifications

| | |
|----------------------------|---|
| DEVICE TYPE | Plug |
| TYPE | Plug |
| AMPERAGE RATING | 15A |
| VOLTAGE RATING | 250V |
| CONTACT MATERIAL | Brass |
| APPLICATION | Industrial |
| DEVICE GRADE | Extra heavy-duty industrial specification grade |
| WIRING METHOD | Back wire |
| NUMBER OF WIRES | 3 |
| NUMBER OF POLES | Two-pole |
| STYLE TYPE | Straight body |
| CORD RANGE | 0.33-0.66" in diameter |
| MATERIAL | Nylon |
| PACKAGING TYPE | Core pack |
| COLOR | Black White |
| CONNECTION TYPE | Screw |
| ALLOWABLE WIRE SIZE | #18-12 AWG |
| NEMA CONFIGURATION | 6-15P |
| TORQUE RATING | 14 lbf-inch |
| DESIGN TYPE | Straight blade |
| FACE/BODY MATERIAL | Nylon |
| RECEPTACLE TYPE | Two-pole, three-wire, grounding |

Resources

| | |
|-------------------------------|--|
| MULTIMEDIA | Arrow Hart - Connecting Safety to Reliability since 1890 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - 5666N Arrow Hart industrial grade straight blade and locking devices brochure |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

