

Eaton 5710N

Catalog Number: 5710N

Eaton Arrow Hart extra heavy-duty auto grip plug , #12-4 AWG, 50A, Industrial, 250V, Back wire, Gray, Brass, Nylon, 6-50P, Two-pole, three-wire, grounding, Screw, Nylon, Core pack



General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty auto grip plug	5710N
	UPC
	040893020273
Product Length/Depth	Product Height
6.938 in	3.375 in
Product Width	Product Weight
3.61 in	0.79 lb
Warranty	Certifications
Refer to warranty document.	cULus Listed
	NOM
	Federal Specification Classification 6221 02

Product specifications

Device type

Plug

Color

Gray

Face/body material

Nylon

Wiring method

Back wire

Material

Nylon

Allowable wire size

#12-4 AWG

Amperage Rating

50 A

Number Of Poles

Two-pole

Contact material

Brass

Type

Plug

Device grade

Extra heavy-duty industrial specification grade

NEMA configuration

6-50P

Style type

Power, Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section A](#)

Specifications and datasheets

[Eaton Specification Sheet - 5710N](#)

250V

Application

Industrial

Torque rating

30-35 lbf-inch

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)