

Eaton 5759

Catalog Number: 5759

Eaton power device receptacle, #12 - 4 AWG, 20A, Flush, 125/250V, Back, Black, NEMA 14-20R, Three-pole, Four-wire, Three-pole, four-wire, grounding, Screw, Glass-filled nylon, Power

General specifications

Product Name	Catalog Number
Eaton power device receptacle	5759
UPC	Product Length/Depth
040893015408	1.88 in
Product Height	Product Width
4.13 in	1.63 in
Product Weight	Compliances
0.19 lb	RoHS Compliant

Product specifications

Color

Black

Wiring method

Back

Material

Glass filled nylon

Mounting method

Flush

Allowable wire size

#12-4 AWG

Amperage Rating

20A

Number Of Poles

Three-pole

NEMA configuration

14-20R

Design type

Receptacle

Connection type

Screw

Style

Power

Number of wires

4

Receptacle type

Three-pole, four-wire, grounding

Voltage rating

125/250 V

Torque rating

25 lbf-inch

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section A](#)

Specifications and datasheets

[Eaton Specification Sheet - 5759](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)