

Straight Blade Receptacle 3-Pole 4-Wire 60A 250V



## Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007576009
Country Of Origin	China	Number of Receptacles	1
Features	Durable	Outlet Type	Straight Blade
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

### Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
------------	-----	---------------------	--------

---

cULus Listed

Yes

CSA File Number

16063

---

**Technical Information**

---

Number of Wires

4

Amperage

60 A

---

Number of Poles

3-Way

Indoor/Outdoor

Indoor

---

NEMA Configuration Code

15-60

Voltage

250.0 V

---

Straight Blade Receptacle 3-Pole 4-Wire 60A 250V



## Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007576009
Country Of Origin	China	Number of Receptacles	1
Features	Durable	Outlet Type	Straight Blade
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

### Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
------------	-----	---------------------	--------

---

cULus Listed	Yes	CSA File Number	16063
--------------	-----	-----------------	-------

---

### Technical Information

---

Number of Wires	4	Amperage	60 A
-----------------	---	----------	------

---

Number of Poles	3-Way	Indoor/Outdoor	Indoor
-----------------	-------	----------------	--------

---

NEMA Configuration Code	15-60	Voltage	250.0 V
-------------------------	-------	---------	---------

---