



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

555 E. 15th Street  
72701-0000, AR Fayetteville  
Phone: 479-443-4948  
Fax: 479-443-6465



## 600L2 600L2 *Nsi Industries*

Catalog Number	600L2
Manufacturer	Nsi Industries
Description	Panelboard Lug, #4 Awg Conductor Size, #2 Awg Conductor Size, Non-Insulated, Aluminum/Copper Conductor Material, 1 Conductor, +90 °C Operating Temperature, 4.65 In Overall Length, Screw Terminal, 600 V, 0.46 LB/Ea
Weight per unit	0.4600 (lbs/each)
Product Category	Large Terminals & Connectors

## Features

Warranty	1 YEAR
----------	--------

## Descriptions

Description	600L2
extra long description	NSI 600L2 Nema Panel Lug 600-2
Features	1 Port Panelboard Lug 600 MCM - 2 AWG Panelboard style for multi-conductor with NEMA mounting hole spacing for turn prevent and secureness. Made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. For use with copper or aluminum conductors. Rated 600 volts (2000V max per UL486B). UL 486A/B Listed. Temperature rating 90 degrees C. All hole spacing is NEMA standard of 1.750".

## Manufacturer Information

GTIN	00662381001320
UPC	662381001320

## Packaging

Carton	1
Weight Per each	0.46