



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2108 South Huber
79007-0000, TX Borger
Phone: 806-273-3085
Fax: 806-273-2487



6010ADW25 14-1/2-26-1/2 Adj Bar HNGR

Abb Installation Products, Inc

Catalog Number	6010ADW25
Manufacturer	Abb Installation Products, Inc
Description	Adjustable Bar Hanger. Depth 1-3/16 Inch. For 3/8 Inch, 1/2 Inch and 5/8 Inch Wall Board and Plaster. Score Marks For Drywall and Plaster Depths. Maximum Load Capacity: 50 Pounds (22.7 Kilograms). Length: 14-1/2 Inches to 26-1/2 Inches. Packaged Complete With Stud.
Weight per unit	0.6250 (lbs/each)
Product Category	Bar Hangers & Outlet Box Accy.

Features

Knockouts	FALSE
Material	Steel

Material, Color, and Finish

Color	Silver
-------	--------

Dimensions and Weight

Size	Length from 14-1/2 Inches to 26-1/2 Inches
------	--

Descriptions

Description	14-1/2-26-1/2 ADJ BAR HNGR
extra long description	ABB 6010ADW-25 14-.5 IN-26-.5 IN,BA
Long Description	Adjustable bar hanger. Depth 1-3/16 inch. For 3/8 inch, 1/2 inch and 5/8 inch wall board and plaster. Score marks for drywall and plaster depths. Maximum load capacity: 50 pounds (22.7 kilograms). Length: 14-1/2 inches to 26-1/2 inches. Packaged complete with stud.
Product Type	14-.5 In-26-.5 In, Bar Hanger, W/Stud
Special Features	Claws provide temporary support for proper positioning until permanently installed

Manufacturer Information

Brand	Steel City
GTIN	00785991154504
Manufacturers Part Number	6010ADW-25
UPC	785991154504

Taxonomies, Classifications, and Categories

Category Description	CONDUIT HANGERS/STAND OFF STRAPS
Type	Bar Hangers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2108 South Huber
79007-0000, TX Borger
Phone: 806-273-3085
Fax: 806-273-2487

Packaging

Carton 25

Weight Per each 0.625

Uses, Certifications, and Standards

Application For use with 3/8 inch, 1/2 inch & 5/8 inch wall board and plaster

standard UL E13938, CSA 12798 / UL E13938, CSA 12798