



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



6010DW25 10 1/2-18 1/2 HGR&Stud 50LB

Thomas&Betts-Abb Ins Prod

Catalog Number	6010DW25
Manufacturer	Thomas&Betts-Abb Ins Prod
Description	Adjustable Bar Hanger, Steel, Silver, 0.48 LB/Ea
Weight per unit	0.4800 (lbs/each)
Product Category	Bar Hangers & Outlet Box Accy.

Features

Knockouts	NO
-----------	----

Dimensions and Weight

Size	Length from 10-1/2 Inches to 18-1/2 Inches
------	--

Descriptions

Description	10 1/2-18 1/2 HGR&STUD 50LB
Special Features	Claws provide temporary support for proper positioning until permanently installed.

Manufacturer Information

Brand	SC Ind Box/Covr
GTIN	00785991154658
UPC	785991154658

Taxonomies, Classifications, and Categories

Category Description	CONDUIT HANGERS/STAND OFF STRAPS
Type	Bar Hangers

Packaging

Carton	25
Weight Per each	0.48

Uses, Certifications, and Standards

Application	For use with 3/8 inch, 1/2 inch & 5/8 inch wall board and plaster.
standard	UL E13938, CSA 12798

Bar Hangers and Brackets



BCBK-01



BCBK-20



6010DW-25 / 6010ADW-25



6011DW-25 / 6011ADW-25



CI1060



Cat. No.	Description
Bar Hangers	
BCBK-01	Adjustable hanger for wood stud. Length: 15.5 in. Height: 2.5 in.
BCBK-20	Adjustable hanger for octagonal boxes for furring channel. Width: 4-1/2 in. x Height: 1-3/8 in. x Length: 21-1/8 in.
CI1060	Length: 16 in. Grooved for box ears



Cat. No.	Description	Maximum load capacity	Length
Adjustable bar hangers for 3/8 in., 1/2 in. and 5/8 in. drywall and plaster			
6010DW-25	Score marks for drywall and plaster depths. Packaged complete with stud.	50 lb. (22.7 kg)	10-1/2 in. to 18 in.
6010ADW-25			14-1/2 in. to 25 in.
6011DW-25	Score marks for drywall and plaster depths. Packaged complete with fastener.		10-1/2 in. to 18 in.
6011ADW-25			14-1/2 in. to 25 in.

* These products replace Iberville® BC1041 and BC1042 bar hangers.

Bar Hangers and Brackets

Extra heavy-duty new work bar hanger Ceiling fan and light fixture bar hanger

This innovative extruded-aluminum bar hanger was designed for strength. It is cULus Listed for up to 70 lb. for fan support and an industry-leading 200 lb. for fixture support.

- Gold Glav-Krom™ finish on mounting screws easily identifies hanger as meeting CEC & cULus requirements for fan or light fixture
- Screwed-on end plates are consistently strong and avoid unsightly welds
- End plates feature temporary fixing spikes for hands-free installation
- Expandable for joints spaced from 14.5 to 24 in.



Cat. No.	Description	Volume (Cu. in.)
54151CFB-NW	New work bar hanger with 4 in. octagonal 1-1/2 in. deep box with NMD90 cable clamps. (wood screws included) Maximum load capacity: Fan 70 lb. and fixture 200 lb.	15.8

Bar Hangers and Brackets

Extra heavy-duty rework bar hanger

Ceiling fan and light fixture bar hanger

Exhaustive research and development has resulted in an innovative of ceiling fan support boxes that give Thomas & Betts the competitive advantage. Ceiling fan and fixture installation is faster, easier and safer with Steel City® ceiling fan support boxes.

- Gold Glav-Krom™ finish on mounting screws easily identifies hanger as meeting CEC & cULus requirements for fan or light fixture
- cULus Listed up to 70 lb. for fan and 200 lb. for light fixture
- Square end plates keep the bar parrallel with sheetrock
- Expandable for joints from 14.5 to 24 in.



Cat. No.	Description	Volume (Cu. in.)
54151CFB-0W	Rework bar hanger with 4 in. octagonal 1-1/2 in. deep box with NMD90 cable clamps. Maximum load capacity: Fan 70 lb. and fixture 200 lb.	15.8