



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

601266607 16/2 SPT2 Lamp Cord 250' Reel 300V Brown Jacket

Coleman Cable

Catalog Number	601266607
Manufacturer	Coleman Cable
Description	Cable, SPT-2; 300 V Voltage Rating; Conductor Material Bare Copper; Brown Jacket Color; PVC Insulation Material; 2 Conductor(S); 16 Awg Conductor; 26/30 Strands; Outer Diameter 0.155 Inch X 0.303 Inch; Temperature Rating -20 to 60 Deg C
Weight per unit	0.0400 (lbs/ft)
Product Category	Portable Cord Sets

Features

Conductor Size	16 AWG
Number of Conductors	2 IN
Stranding	26/30 STRANDS
Voltage Rating	300 V

Material, Color, and Finish

Conductor Material	BARE COPPER
Insulation Material	PVC
Jacket Color	BROWN

Dimensions and Weight

Length	250 FT
Length in ft	250 VAC
Outer Diameter	0.156 Inch x 0.307 Inch

Descriptions

Additional Information	ROHS Compliant; Applicable Standard NEC 400; Insulation Thickness 0.048 Inch; Insulated Conductor Diameter 0.155 Inch x 0.303 Inch
Commodity Description	CORDS SETS
Description	16/2 SPT2 LAMP CORD 250' REEL 300V BROWN JACKET
Long Description	CABLE, SPT-2; 300 V VOLTAGE RATING; CONDUCTOR MATERIAL BARE COPPER; BROWN JACKET COLOR; PVC INSULATION MATERIAL; 2 CONDUCTOR(S); 16 AWG CONDUCTOR; 26/30 STRANDS; OUTER DIAMETER 0.155 INCH X 0.303 INCH; TEMPERATURE RATING -20 TO 60 DEG C
Product Type	Cable

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892612672
Manufacturers Part Number	49914502
Model	601 A
UPC	029892612672



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Portable Cords, Voice, Data, Video Wire & Cable
Type	SPT-2

Packaging

Carton	250
Weight Per foot	0.04

Uses, Certifications, and Standards

Application	Table Lamp, Sawg Lamp
Approval	UL 62, CSA 22.2
Temperature Rating	-20 TO 60 DEG C

Seoprene® 105 Control Cable



Cable ranges from 18-10 AWG with 5 or more conductors. Provides lightweight flexibility and mechanical toughness in a multi-conductor construction that is easy to strip. Rated 600V with temperature ratings from -50C to 105C. Applications include power in processing facilities, push-button line controls, 600V control and instrumentation, temperature, motor and robotic control systems. UL Listed, CSA Certified, MSHA approved for flame resistant mining applications.



CAT NO	SIZE	TYPE	JACKET COLOR	WT/ 1000'
30505-xx-08	18/5	SE00W	Black	113
30605-xx-08	18/6	SE00W	Black	119
30805-xx-08	18/8	SE00W	Black	151
31005-xx-08	18/10	SE00W	Black	168
31205-xx-08	18/12	SE00W	Black	212
31405-xx-08	18/14	SE00W	Black	235
31605-xx-08	18/16	SE00W	Black	277
30506-xx-08	16/5	SE00W	Black	140
30606-xx-08	16/6	SE00W	Black	158
30706-xx-08	16/7	SE00W	Black	165
30806-xx-08	16/8	SE00W	Black	190
31006-xx-08	16/10	SE00W	Black	242
31206-xx-08	16/12	SE00W	Black	288
31406-xx-08	16/14	SE00W	Black	311
31606-xx-08	16/16	SE00W	Black	355
30507-xx-08	14/5	SE00W	Black	232
30607-xx-08	14/6	SE00W	Black	269
30707-xx-08	14/7	SE00W	Black	280
31007-xx-08	14/10	SE00W	Black	423
31207-xx-08	14/12	SE00W	Black	465
30508-xx-08	12/5	SE00W	Black	302
30608-xx-08	12/6	SE00W	Black	343
30808-xx-08	12/8	SE00W	Black	416
30509-xx-08	10/5	SE00W	Black	387

Put-up: xx= 250' (04); 500' (05); 1000' (06)

Lamp Cord



For use with lamps and other small appliances.



60000

CAT NO	WIRE GAUGE	DESCRIPTION	JACKET COLOR	STRANDING	NOMINAL WALL	NOMINAL O.D.	LENGTH IN FT	MASTER WT
60000-66-01	18/2	SPT-1	White	41/34	.033	.115 x .250	250	7
60000-66-07	18/2	SPT-1	Brown	41/34	.033	.115 x .250	250	7
60000-66-08	18/2	SPT-1	Black	41/34	.033	.115 x .250	250	7
60000-66-18*	18/2	SPT-1	Clear	41/34	.033	.115 x .250	250	7
60000-66-19*	18/2	SPT-1	Gold	41/34	.033	.115 x .250	250	7
60000-66-21*	18/2	SPT-1	Silver	41/34	.033	.115 x .250	250	7
60126-66-01	16/2	SPT-2	White	26/30	.048	.156 x .307	250	10
60126-66-07	16/2	SPT-2	Brown	26/30	.048	.156 x .307	250	10
60126-66-08	16/2	SPT-2	Black	26/30	.048	.156 x .307	250	10

* Not CSA Listed

